

NAM

C20



armas
ELEKTRONİK

Contact-Free and Rapid Breath Alcohol Tester

ARMAS introduces the series of breath alcohol testers NAM-C20, featuring two models: the NAM-C20 for contactless measurement with a specially designed funnel and the NAM-C20M with a disposable mouthpiece for testing.

The models are equipped with a user-friendly, sunlight-readable color display. Measurement results can be shown in either a qualitative format (icons: tick – no alcohol, exclamation mark – critical alcohol level (if set), cross mark – alcohol) or a quantitative format (measured value with the preset unit and corresponding icon) based on the selected menu settings. Additionally, the NAM-C20 features multiple LEDs, ensuring results are easily visible from a distance or via a security camera.

The devices are specifically designed for alcohol detection in environments where rapid testing is required, including construction sites, mining facilities, factories, stadiums, driver assembly points, as well as hotels, restaurants, and areas requiring occupational health and safety compliance.

Furthermore, breath alcohol testers serve as an effective tool for security forces conducting preliminary field assessments. With a capacity to perform up to 14 rapid measurements per minute, the handheld devices ensure high operational efficiency while minimizing consumable material usage, providing a cost-effective solution.



Suitable for Versatile Applications and Conditions

The NAM-C20 series alcohol measurement system features multiple testing modes: **Automatic** mode for individuals who can blow, **Passive** mode for environmental testing, and **Manual** mode for those unable to blow sufficiently. Furthermore, individuals who refuse to take the test can be logged using the **Test Refusal** mode.

The NAM-C20 series breath alcohol tester features a mounting area on the back that allows the use of a ¼-inch selfie stick, providing the opportunity to extend the device to the driver in vehicles such as trucks and large vehicles, facilitating the testing process. The models function with alkaline batteries, with the option to select a rechargeable li-ion battery upon request.

The computer data software enables the transfer of measurement results from the handheld device to a PC. Additionally, the NAM-C20M model is available with an optional thermal Bluetooth printer for result reporting.

NAM-C20



The contact-free funnel of the NAM-C20 breathalyzer features a special design that enables both automatic and passive measurements by detecting exhalations from a certain distance. The funnel prevents residues from reaching the device's alcohol sensor, thereby extending the sensor's lifespan. Its unique airflow channel design ensures that the exhaled breath of the person being tested does not flow back towards their face, eliminating the risk of infection among users and ensuring a hygienic and safe breath alcohol testing process.

The model NAM-C20 features the capability to emit lights in various colors to display measurement results. Additionally, the device serves as a warning signal in roadside applications to alert drivers. The warning lights can be customized to different colors and set to either a steady or flashing mode based on the specific situation.

Emergency (Police): Red-Blue Warning Mode

Emergency: Yellow Flashing Warning Mode

Safe: Steady Green Warning Mode

Information/Instruction: Blue Warning Mode

General Information: Steady White Warning Mode



NAM-C20M

The model NAM-C20M features a portable, handheld design for effortless use. In addition to displaying real-time measurement results, the product offers the option to generate instant reports via an optional Bluetooth printer. Additionally, users can conveniently print stored data from the device's memory at a later time.

Designed as a preliminary screening breathalyzer, the NAM-C20M becomes operational within seconds and allows for rapid, consecutive measurements. The specially designed, hygienically packaged, single-use mouthpiece ensures maximum user health and safety. The contact-free funnel can also be attached and effectively used for alcohol level measurement in all testing modes.




CALIBRATION
Gas or Vapor
(Bath)


MEMORY
7500-35000


SCREEN
Color TFT


DATA TRANSFER
Transfer to PC


SENSOR
Electrochemical
Fuel Cell


WORKING TEMPERATURE
-10°C to +50°C


PRINTER
Thermal Bluetooth
(Optional)


START UP TIME
Less than
2.5 seconds


WIRELESS COMMUNICATION
Bluetooth
(optional for Printer)

